

English	Wall switch functionality	2
Deutsch	Coming soon	
Français	Coming soon	
Dansk	Coming soon	
Nederlands	Coming soon	
Italiano	Coming soon	
Español	Coming soon	
Bosanski	Coming soon	
Български	Coming soon	
Česky	Coming soon	
Eesti	Coming soon	
Hrvatski	Coming soon	
Latviski	Coming soon	
Lietuvių	Coming soon	
Magyar	Coming soon	
Norsk	Coming soon	
Polski	Coming soon	
Português	Coming soon	
Română	Coming soon	
Русский	Coming soon	
Slovenščina	Coming soon	
Slovensky	Coming soon	
Srpski	Coming soon	
Suomi	Coming soon	
Svenska	Coming soon	
Türkçe	Coming soon	
Українська	Coming soon	

Keys for operating the product **a**

⬆️ OPEN/UP or ⬆️ CLOSE/DOWN


Short key pressure: Product will travel to maximum top or bottom position.

Long key pressure: Product will travel only until the key is released.

Note: If several electrical products are connected to a control unit KLC 500, only one of the products (at random) can be operated in this way.

STOP key **b**

⊙ Product stops.




Wall switch KLI has two buttons used for setup:



The GEAR button "Open for registration".



The PAIR button "Register".



To push the buttons, use a pointed object.

